

WATER FILTRATION FOR INFECTION CONTROL

Aqua free

Baclyser Inline Filters IL

Disposable Baclyser Inline Filters are FDA Medical Devices that protect against dangerous waterborne pathogens such as Legionella and Pseudomonas. Baclyser filters have a rated life of 6 months and are available in three sizes:

Baclyser IL10 (Part #49408) Baclyser IL5 (Part #49406) Baclyser IL3 (Part #49404) Maximum Filter Life is 6 months Maximum Filter Life is 6 months Maximum Filter Life is 6 months



Baclyser Inline Filters IL10, IL5, IL3

Benefits of Baclyser Inline Filters:

- Point-of-use (POU) 0.20 μm membrane filtration provides immediate and long-term protection against Legionella and other waterborne pathogens.
- Inlet and outlet connections are 1/2" male pipe thread which allow for a variety of direct connection options using off-the-shelf plumbing components.
- High flow rate and capacity.
- Can be used in combination with secondary water disinfection chemical treatment systems.
- Three sizes of filters are available providing more options for tight space installations.
- No hazardous waste disposal or "Red Bag" restrictions required.

PBIL-4.0

For Use In: hospitals, clinics, and other medical facilities such as skilled nursing and adult care facilities. Recommended for areas at high-risk for hospital-acquired infections (HAIs) such as ICU, neonatal, oncology, burn, and transplant units.

..........



Baclyser Inline Filters IL

| Specifications | Baclyser IL3 | Baclyser IL5 | Baclyser IL10 |
|----------------------------------|-------------------------|-------------------------|-------------------------|
| Part Number | 49404 | 49406 | 49408 |
| Membrane Material | Polysulfone (PSU) | Polysulfone (PSU) | Polysulfone (PSU) |
| Membrane Type | Asymmetric, hydrophilic | Asymmetric, hydrophilic | Asymmetric, hydrophilic |
| | hollow fibers | hollow fibers | hollow fibers |
| Maximum Pore Size | 0.20 μm | 0.20 μm | 0.20 μm |
| Bacterial Retention ¹ | >99.99999% (>7 log) | >99.99999% (>7 log) | >99.99999% (>7 log) |
| Maximum Filter Life ² | 6 months | 6 months | 6 months |
| Maximum Inlet Pressure | 75 psi | 75 psi | 75 psi |
| Maximum Temperature | 104 °F | 104 °F | 104 °F |
| Dimensions | 4.7" x 1.8" | 6.0" x 2.4" | 8.4" x 2.7" |
| Connection | 1/2" male pipe | 1/2" male pipe | 1/2" male pipe |
| Housing Material | ABS | ABS | ABS |
| O-ring Material | Nitrile | Nitrile | Nitrile |
| Flow Rate (@72 psi) | 3.4 GPM | 5.8 GPM | 7.9 GPM |
| Estimated Capacity ² | 800 gallons | 3,400 gallons | 15,000 gallons |
| Chlorine Resistance ³ | ≤10 ppm | ≤10 ppm | ≤10 ppm |

¹Third party tested for bacterial retention of *B. diminuta* to ASTM F838-05 for sterilizing grade filters.

² Depending on the quality of influent water.

³ Continuous dosage of ≤10 ppm over operating time; short term (1h) high dosage (400,000 ppm h) for chemical disinfection.

Related Parts

| Part # | Description | | |
|--------|--|--|--|
| QCK02 | Baclyser Inline Direct Installation | | |
| QCK03 | Baclyser Inline Series 40 New Installation Kit | | |
| QCK04 | Baclyser Inline Series 40 Replacement Kit | | |
| QCK05 | Baclyser Inline Series 50 Replacement Kit | | |
| QCK06 | Baclyser Inline Series 50 New Installation Kit | | |
| QCK09 | Baclyser Inline Screw-On Push Connect Kit | | |

Quick Connection Kits provide end users the parts needed to quickly and cost-effectively install Baclyser Inline Filters in a variety of plumbing configurations. Contact us with any questions or if you need assistance.

About AquaMedix

AquaMedix develops, manufactures, and distributes point-of-use (POU) and inline filtration systems designed to protect against waterborne bacteria. Proprietary filters trap potentially lethal pathogenic bacteria such as Legionella, Pseudomonas, Acinetobacter, Nontuberculous Mycobacterium, and Stenotrophomonas. In addition to selling a complete line of CleanSpray POU and inline filtration systems, AquaMedix is the U.S. Master Distributor for Baclyser POU and inline filters by Aqua *free*.

Our products include shower and faucet filters as well as standard and specialty inline filters to protect water used in ice machines, coffee machines, dental office sprayers, and other appliances. AquaMedix products are easy to install and maintain without large capital expenses or the need for costly chemicals, machinery, or special training. With filters installed nationwide in healthcare facilities, AquaMedix is positioned to address infection control concerns with a variety of innovative and cost-effective products.

AquaMedix, LLC | 7169 Shady Oak Rd, Minneapolis, MN 55344 | Tel. 952-479-0636 | www.aquamedix.net

FDA Class I Medical Device. Filters are intended for use on visually clear drinking water that meets all other public health standards. Filters are not intended for reducing pathogenic virus particles. Filter not for use with any injection or infusion applications or applications requiring United States Pharmacopeia sterile water. The information provided in this literature was reviewed for accuracy at the time of publication. Product data may be subject to change. For current information contact AquaMedix. Any appliance or equipment utilizing these filters must be maintained, disinfected, and sanitized according to the manufacturer's instructions.